



The specifications for this control system are all listed on the website product page. To request a PDF brochure formatted data sheet, please use the "Ask an Engineer" portal on the web page and we will email you the PDF data sheet.

PRE-CONFIGURED SYSTEM INCLUDES

		
18 Amp Current Source; 128 Watt TEC Controller	Pre-Configured TEC Cooled Laser Diode Heat Sink	All Required Connecting Cables



control system does not include laser diode

LASER LAB SOURCE
WORLD LEADING PRODUCTS
FOR LASER SCIENTISTS AND ENGINEERS